TPM121ZTM-12/800330904 S00072 - Panel PC

2401306

https://www.phoenixcontact.com/us/products/2401306

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Maritime-Panel PC; 30.7 cm / 12.1"-TFT display (analog resistive (polyester)); 1280 x 800 pixel(s) (WXGA); 262144 colors; Processor: Intel® Atom™ E680T 1.6 GHz; Interfaces: 4x USB Host 2.0, 2x Ethernet (10/100/1000 Mbps), RJ45; Operating system: Windows® Embedded Standard 7; Software: Movicon™ Demo Runtime; without bus system

Commercial data

Item number	2401306
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCBBC
GTIN	4055626107561
Weight per piece (including packing)	2,100 g
Weight per piece (excluding packing)	2,100 g
Country of origin	DE

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area

Product properties

Product type	Panel PC
Application	Maritime

Computer data

Processor	Intel® Atom™ E680T 1.6 GHz
Operating system	Windows® Embedded Standard 7
RAM	2 GB DDR2 SDRAM
Data storage system	SATA DOM SSD (SLC), 8 GB
Cooling	passive
Slots	1x SD
Extras	Maritime with keys

Display

Display type	30.7 cm / 12.1"-TFT
Screen resolution	1280 x 800 Pixel(s) (WXGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	320 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	262144 colors
Reading angle left	88.00 °
Reading angle right	88.00 °
Reading angle top	88.00 °
Reading angle bottom	88.00 °

System properties

User software	Movicon™ Demo Runtime

Electrical properties

Service life of battery	5 years (typical)

Supply

Power supply unit	24 V DC ±20 %
Typical current consumption	0.9 A

Real-time clock

Real-time clock	Yes

Interfaces

Interfaces	4x USB Host 2.0
Network	2x Ethernet (10/100/1000 Mbps), RJ45
Bus system	without bus system

Dimensions

External dimensions

Width / Height / Depth	336 mm / 252 mm / 5 mm (Dimensions of the front plate)
	/ / 82 mm (without serial interface)

Installation dimensions

Width / Height / Installation depth	310 mm / 226 mm / 100 mm (Mounting cutout, depth with serial interface)

Material specifications

Material front plate	Aluminum (black anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	0 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	0.7g, in accordance with EN 60068-2-6

Mounting

Mounting type	Front mounting

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com