

TP121GTS/700330004 S00103 - Panel PC



2401448

<https://www.phoenixcontact.com/us/products/2401448>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel PC, 30.7 cm / 12.1"-TFT display (analog resistive (polyester)), 800 x 600 pixel(s) (SVGA), 262144 colors, AMD® Embedded G-Series (T40R), 1 GHz, 4x USB Host 2.0, 2x Ethernet (10/100/1000 Mbps), RJ45, Windows® Embedded Standard 7, Open platform, without bus system.

Commercial data

Item number	2401448
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRBACB
GTIN	4055626157627
Weight per piece (including packing)	2,400 g
Weight per piece (excluding packing)	2,400 g
Country of origin	DE

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Panel PC
--------------	----------

Computer data

Processor	AMD® Embedded G-Series (T40R), 1 GHz
Operating system	Windows® Embedded Standard 7
RAM	2 GB DDR2 SDRAM
Data storage system	None installed
Slots	1x SD

Display

Display type	30.7 cm / 12.1"-TFT
Screen resolution	800 x 600 Pixel(s) (SVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	360 cd/m ² typical (adjustable)
MTBF	50000 h
Color spectrum	262144 colors
Reading angle left	80.00 °
Reading angle right	80.00 °
Reading angle top	65.00 °
Reading angle bottom	75.00 °

System properties

User software	Open platform
---------------	---------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Real-time clock

Realtime clock	Yes
----------------	-----

Supply

Power supply unit	24 V DC ±20 %
-------------------	---------------

Interfaces

Interfaces	4x USB Host 2.0
Network	2x Ethernet (10/100/1000 Mbps), RJ45

2401448

<https://www.phoenixcontact.com/us/products/2401448>

Bus system	without bus system
------------	--------------------

Dimensions

External dimensions

Width / Height / Depth	340 mm / 270 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	315 mm / 99 mm / 244 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

2401448

<https://www.phoenixcontact.com/us/products/2401448>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com