

TP121SKM200114041 S00127 - Touch panel



2401554

<https://www.phoenixcontact.com/us/products/2401554>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 30.7 cm / 12.1"-TFT display (projective-capacitive (PCAP)), 1280 x 800 pixel(s) (WXGA), 65536 colors, Arm® Cortex®-A8, 1000 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7, IniNet Browser, without bus system.

Similar figure

Commercial data

Item number	2401554
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCADD
GTIN	4055626228891
Weight per piece (including packing)	1,700 g
Weight per piece (excluding packing)	1,700 g
Country of origin	DE

Technical data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm® Cortex®-A8, 1000 MHz
Operating system	Windows® Embedded Compact 7
RAM	1 MB SRAM
	512 MB LPDDR SDRAM
Data storage system	NAND-Flash, 1 GB
Slots	1x SD

Display

Display type	30.7 cm / 12.1"-TFT
Screen resolution	1280 x 800 Pixel(s) (WXGA)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	320 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	65536 colors
Reading angle left	88.00 °
Reading angle right	88.00 °
Reading angle top	88.00 °
Reading angle bottom	88.00 °

Interfaces

Interfaces	2x USB Host 2.0
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

System properties

User software	IniNet Browser
---------------	----------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Power supply unit	24 V DC ±20 %
Typical current consumption	0.9 A

Real-time clock

Realtime clock	Yes
----------------	-----

Mounting

Mounting type	Front mounting
---------------	----------------

TP121SKM200114041 S00127 - Touch panel



2401554

<https://www.phoenixcontact.com/us/products/2401554>

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 45 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	336 mm / 234 mm / 6 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	329 mm / 227 mm / 53 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

TP121SKM200114041 S00127 - Touch panel



2401554

<https://www.phoenixcontact.com/us/products/2401554>

Classifications

UNSPSC

UNSPSC 21.0	43211904
-------------	----------

2401554

<https://www.phoenixcontact.com/us/products/2401554>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com