

TP121SKM/200114041 S00068 - Touch panel



2401638

<https://www.phoenixcontact.com/us/products/2401638>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 30.7 cm / 12.1"-TFT display (projective-capacitive (PCAP)), 1280 x 800 pixel(s) (WXGA), 65536 colors, Arm® Cortex®-A8, 1000 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7, Movicon™, without bus system.

Similar figure

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2401638 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | DRCADC |
| GTIN | 4055626314495 |
| Weight per piece (including packing) | 2,700 g |
| Weight per piece (excluding packing) | 2,700 g |
| Country of origin | DE |

Technical data

Notes

Utilization restriction

| | |
|----------|---------------------------------------------------------------------------|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---------------------------------------------------------------------------|

Product properties

| | |
|--------------|----------------|
| Product type | Operator panel |
|--------------|----------------|

Computer data

| | |
|---------------------|-------------------------------------|
| Processor | Arm® Cortex®-A8, 1000 MHz |
| Operating system | Windows® Embedded Compact 7 |
| RAM | 1 MB SRAM 512 MB LPDDR RAM |
| Data storage system | NAND-Flash, 1 GB |
| Slots | 1x SD |
| Extras | Integrated acoustic signal (buzzer) |

Display

| | |
|-----------------------|--------------------------------------------|
| Display type | 30.7 cm / 12.1"-TFT |
| Screen resolution | 1280 x 800 Pixel(s) (WXGA) |
| Touch technology | projective-capacitive (PCAP) |
| Display lighting type | LED |
| Brightness | 320 cd/m ² typical (adjustable) |
| MTBF | 50000 h |
| Color spectrum | 65536 colors |
| Reading angle left | 88.00 ° |
| Reading angle right | 88.00 ° |
| Reading angle top | 88.00 ° |
| Reading angle bottom | 88.00 ° |

Interfaces

| | |
|------------|----------------------------------|
| Interfaces | 2x USB Host 2.0 |
| Network | 1 x Ethernet (10/100 Mbps), RJ45 |
| Bus system | without bus system |

System properties

| | |
|---------------|----------|
| User software | Movicon™ |
|---------------|----------|

Electrical properties

| | |
|-------------------------|-------------------|
| Service life of battery | 5 years (typical) |
|-------------------------|-------------------|

Supply

| | |
|-------------------|---------------|
| Power supply unit | 24 V DC ±20 % |
|-------------------|---------------|

2401638

<https://www.phoenixcontact.com/us/products/2401638>

| | |
|--------------------------|-------|
| Max. current consumption | 0.9 A |
|--------------------------|-------|

Real-time clock

| | |
|----------------|-----|
| Realtime clock | Yes |
|----------------|-----|

Mounting

| | |
|---------------|----------------|
| Mounting type | Front mounting |
|---------------|----------------|

Material specifications

| | |
|----------------------|-----------------------------|
| Material front plate | Aluminum (natural anodized) |
| Housing material | Steel sheet, zinc-plated |

Environmental and real-life conditions

Ambient conditions

| | |
|-----------------------------------------|--------------------------------------|
| Degree of protection | IP65 (front), IP20 (back) NEMA 4X |
| Ambient temperature (operation) | 0 °C ... 50 °C |
| Ambient temperature (storage/transport) | -25 °C ... 70 °C |
| Altitude | 3000 m |
| Permissible humidity (operation) | 20 % ... 85 % |
| Shock | 15g, according to IEC 60068-2-27 |
| Vibration (operation) | 1g, according to EN 60068-2-6 |

Dimensions

External dimensions

| | |
|------------------------|--------------------------------------------------------|
| Width / Height / Depth | 336 mm / 244 mm / 6 mm (Dimensions of the front plate) |
|------------------------|--------------------------------------------------------|

Installation dimensions

| | |
|-------------------------------------|-------------------------|
| Width / Height / Installation depth | 326 mm / 224 mm / 53 mm |
|-------------------------------------|-------------------------|

2401638

<https://www.phoenixcontact.com/us/products/2401638>

Environmental product compliance

China RoHS

| | |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-15 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com