

TPE070BKW/A00290029 S00131 - Touch panel



2401659

<https://www.phoenixcontact.com/us/products/2401659>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rugged-Touch panel, 17.8 cm / 7"-TFT display (Projective-capacitive, single-touch control), 800 x 480 pixel(s) (WVGA), 16.7 million colors, Intel® Atom™ E3815 1.46 GHz, 4x USB Host 2.0, 1 x Ethernet (10/100/1000 Mbps), RJ45, Windows® Embedded Compact 7, Open platform, without bus system.

Similar figure

Commercial data

Item number	2401659
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCADA
GTIN	4055626378961
Weight per piece (including packing)	1.1 kg
Weight per piece (excluding packing)	1.1 kg
Country of origin	DE

Technical data

Product properties

Product type	Operator panel
Application	Rugged

Computer data

Processor	Intel® Atom™ E3815 1.46 GHz
Operating system	Windows® Embedded Compact 7
RAM	2 GB DDR3
Data storage system	Flash, 4 GB (integrated)
Slots	1x SD
Extras	Integrated acoustic signal (buzzer)

Display

Display type	17.8 cm / 7"-TFT
Screen resolution	800 x 480 Pixel(s) (WVGA)
Touch technology	Projective-capacitive, single-touch control
Display lighting type	LED
Brightness	400 cd/m ² , typical (adjustable)
MTBF	50000 s
Color spectrum	16.7 million colors
Reading angle left	70.00 °
Reading angle right	70.00 °
Reading angle top	60.00 °
Reading angle bottom	60.00 °

Interfaces

Interfaces	4x USB Host 2.0
Network	1 x Ethernet (10/100/1000 Mbps), RJ45
Bus system	without bus system

System properties

User software	Open platform
---------------	---------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Power supply unit	24 V DC ±20 %
Max. current consumption	0.5 A

Real-time clock

Realtime clock	Yes
----------------	-----

Mounting

TPE070BKW/A00290029 S00131 - Touch panel



2401659

<https://www.phoenixcontact.com/us/products/2401659>

Mounting type	Bolt fixing
---------------	-------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C
Altitude	4000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	234 mm / 174 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	200 mm / 140 mm / 99 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

2401659

<https://www.phoenixcontact.com/us/products/2401659>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com