

# TP105XIT-10/3113C240 S00051 - Touch panel



2401673

<https://www.phoenixcontact.com/us/products/2401673>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 26.4 cm / 10.4"-TFT display (analog resistive (polyester)), 800 x 600 pixel(s) (SVGA), 262144 colors, Xscale® PXA320, 806 MHz, 2x USB host 1.1, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 6.0, Movicon™, PROFIBUS DP.

## Commercial data

Item number	2401673
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCABC
GTIN	4055626379807
Weight per piece (including packing)	1.9 kg
Weight per piece (excluding packing)	1.9 kg
Country of origin	DE

## Technical data

### Product properties

Product type	Operator panel
--------------	----------------

### Computer data

Processor	Xscale® PXA320, 806 MHz
Operating system	Windows® CE 6.0
RAM	128 MB SDRAM
	1 MB SRAM
Data storage system	NAND-Flash, 1 GB
Slots	CompactFlash®
Extras	Integrated acoustic signal (buzzer)

### Display

Display type	26.4 cm / 10.4"-TFT
Screen resolution	800 x 600 Pixel(s) (SVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	340 cd/m <sup>2</sup> typical (adjustable)
MTBF	50000 h
Color spectrum	262144 colors
Reading angle left	70.00 °
Reading angle right	70.00 °
Reading angle top	50.00 °
Reading angle bottom	60.00 °

### Interfaces

Interfaces	2x USB host 1.1
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	PROFIBUS DP

### System properties

User software	Movicon™
---------------	----------

### Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

### Supply

Power supply unit	24 V DC ±20 %
Max. current consumption	0.7 A

### Real-time clock

Realtime clock	Yes
----------------	-----

### Mounting

# TP105XIT-10/3113C240 S00051 - Touch panel



2401673

<https://www.phoenixcontact.com/us/products/2401673>

Mounting type	Front mounting
---------------	----------------

## Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

## Dimensions

### External dimensions

Width / Height / Depth	295 mm / 220 mm / 5 mm (Dimensions of the front plate)
------------------------	--

### Installation dimensions

Width / Height / Installation depth	287 mm / 212 mm / 61 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)