ITC 8113 PW7 - Tablet PC

2402961

https://www.phoenixcontact.com/us/products/2402961

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Tablet PC; 33.8 cm / 13.3"-TFT display (projective-capacitive, ten-touch control); 1920 x 1080 pixel(s) (Full HD); Processor: Intel® Core™ i5 4300U 1.9 GHz; Interfaces: 2x USB 3.0, 1x USB 3.0 inset, WLAN 802.11 a/g/n, Bluetooth 4.0 Class 1+2, 1 x Ethernet (10/100/1000 Mbps), RJ45; Operating system: Windows® 7 Ultimate (64-Bit)



Similar figure

Your advantages

- Optimum performance for every application, thanks to Intel® Celeron® and Intel® Core™ processors
- Stable connections via WLAN and Bluetooth
- Large visualization, thanks to 13.3" display with Full HD resolution
- Sound and proven handling, thanks to enclosed monocoque frame
- Work on the go without interruption, as the battery can be replaced during operation

Commercial data

Item number	2402961
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRBBAF
GTIN	4055626177267
Weight per piece (including packing)	2.2 kg
Weight per piece (excluding packing)	2.2 kg
Country of origin	DE

Technical data

Product properties

Product type	Panel PC

Computer data

Processor	Intel® Core™ i5 4300U 1.9 GHz
Operating system	Windows® 7 Ultimate (64-Bit)
RAM	8 GB DDR3
Data storage system	2.5" SSD, 120 GB (SATA)
Cooling	active
Audio	integrated stereo loudspeakers
	Microphone
Camera	5 megapixels with mechanical autofocus
Optional keys	6 additional keys (on/off button, software keyboard, switch task Alt + ESC, right mouse button, user-specific function, SHIFT key (brightness and volume))

Display

Display type	33.8 cm / 13.3"-TFT
Screen resolution	1920 x 1080 Pixel(s) (Full HD)
Touch technology	projective-capacitive, ten-touch control
Display lighting type	LED
MTBF	> 50000 h
Graphics card	Intel® HD Graphics

Electrical properties

Supply

Power supply unit	20 V/3.5 A external

Energy storage

Number of battery slots	2
Battery technology	Lithium-Ion (Smart battery)

Interfaces

Interfaces	2x USB 3.0
	1x USB 3.0 inset
	WLAN 802.11 a/g/n
	Bluetooth 4.0 Class 1+2
Network	1 x Ethernet (10/100/1000 Mbps), RJ45

Dimensions

Width	356 mm
Height	262 mm
Depth	42 mm

Note on dimensions	73 mm with folded-out supporting feet

External dimensions

Width / Height / Depth	356 mm / 262 mm / 42 mm (73 mm with folded-out supporting feet)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (on the front), IP53 (on the back)
Ambient temperature (operation)	0 °C ... 40 °C
Permissible humidity (operation)	10 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 85 % (non-condensing)

Mounting

Mounting type	Mobile application

Classifications

UNSPSC

UNSPSC 21.0	43211509

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com