

# VISU+ 2 RT-D UNLTD REDNET WEB2 - Visualization software



2403053

<https://www.phoenixcontact.com/us/products/2403053>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Runtime license for Visu+ including redundancy and networking functions and 2 web clients where the I/O data and variables in scripting are not limited. 2 direct driver connections are also supported.

## Your advantages

- Access protection with user management
- Fully scalable process diagrams for using one design on different devices and monitor sizes
- Multilingual software and projects, thanks to Unicode support and online selection
- Full SCADA (Supervisory Control And Data Acquisition) function with visualization, trend representation, and alarm management
- Control coupling with OPC and 2 direct drivers
- Direct driver connection to controllers, e.g., to Siemens S7 or via Modbus/TCP and Modbus/RTU
- Data logging, trend display, and recipe management
- Scripts can be created in VBA and IL

## Commercial data

Item number	2403053
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRDAAB
GTIN	4055626232287
Weight per piece (including packing)	41.5 g
Weight per piece (excluding packing)	39.1 g
Country of origin	DE

# VISU+ 2 RT-D UNLTD REDNET WEB2 - Visualization software



2403053

<https://www.phoenixcontact.com/us/products/2403053>

## Technical data

### Product properties

Product type	Visualization
--------------	---------------

### System properties

Intended use for the software	Visualization
-------------------------------	---------------

### License information

Type of license	Runtime license
-----------------	-----------------

### Functionality

Basic functions	Know-How protection and safety through encoding of projects
	Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server
	FDA CFR 21 Part 11 compatible
Expanded functionality	Web client capability
	Redundancy function
	Networking
Integrated function	Online configuration
	Password protection
	Language selection
	Web client
	Networking
Number of I/O nodes	128000
	Number of clients

### System requirements

Hard disk memory	min. 1 GByte (recommended: 2 GB)
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Italian
Screen resolution	1024 x 768 pixel(s) (XGA)

### System requirements for development environment

Operating equipment	Keyboard, mouse
Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7
	Windows® Embedded Standard 7
	Windows® Server 2019
Windows® Server 2016	

# VISU+ 2 RT-D UNLTD REDNET WEB2 - Visualization software



2403053

<https://www.phoenixcontact.com/us/products/2403053>

	Windows® Server 2012 R2
	Windows® Server 2012
	Windows® Server 2008 R2
	Windows® Server 2008
	Windows® Server 2003

## System requirements for runtime environment

Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7
	Windows® Embedded Standard 7
	Windows® XP Embedded
	Windows® Server 2019
	Windows® Server 2016
	Windows® Server 2012 R2
	Windows® Server 2012
	Windows® Server 2008 R2
	Windows® Server 2008
	Windows® Server 2003
	Windows® CE 5.0
	Windows® CE 6.0
Windows® Mobile	

2403053

<https://www.phoenixcontact.com/us/products/2403053>

## Classifications

### ECLASS

ECLASS-13.0	27242502
-------------	----------

### ETIM

ETIM 9.0	EC001416
----------	----------

### UNSPSC

UNSPSC 21.0	43231500
-------------	----------

2403053

<https://www.phoenixcontact.com/us/products/2403053>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)