

# ITC 8113 GSK 02 - Tablet PC



2403267

<https://www.phoenixcontact.com/us/products/2403267>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Tablet PC, 33.8 cm / 13.3"-TFT display (projective-capacitive, ten-touch control), 1920 x 1080 pixel(s) (Full HD), Intel® Core™ i5 4300U 1.9 GHz, 2x USB 3.0, 1x USB 3.0 inset, WLAN 802.11 a/g/n, Bluetooth 4.0 Class 1+2, 1 x Ethernet (10/100/1000 Mbps), RJ45, Windows® 7 Professional (64-Bit).



Similar figure

## Commercial data

|                       |                                |
|-----------------------|--------------------------------|
| Item number           | 2403267                        |
| Packing unit          | 1 pc                           |
| Note                  | Made to order (non-returnable) |
| Sales key             | DR12                           |
| Product key           | DRBBAF                         |
| GTIN                  | 4055626271569                  |
| Customs tariff number | 84713000                       |
| Country of origin     | DE                             |

## Technical data

### Product properties

|              |          |
|--------------|----------|
| Product type | Panel PC |
|--------------|----------|

### Computer data

|                     |  |
|---------------------|--|
| Processor           | Intel® Core™ i5 4300U 1.9 GHz  |
| Operating system    | Windows® 7 Professional (64-Bit)   |
| RAM                 | 8 GB DDR3  |
| Data storage system | 2.5" SSD, 120 GB (SATA)  |
| Camera              | 5 megapixels with mechanical autofocus   |
| Optional keys       | 6 additional keys (on/off button, software keyboard, switch task Alt + ESC, right mouse button, user-specific function, SHIFT key (brightness and volume)) |

### Display

|                       |  |
|-----------------------|--|
| Display type          | 33.8 cm / 13.3"-TFT                      |
| Screen resolution     | 1920 x 1080 Pixel(s) (Full HD)           |
| Touch technology      | projective-capacitive, ten-touch control |
| Display lighting type | LED                                      |
| MTBF                  | > 50000 h                                |
| Graphics card         | Intel® HD Graphics                       |

### Electrical properties

#### Supply

|                   |                     |
|-------------------|---------------------|
| Power supply unit | 20 V/3.5 A external |
|-------------------|---------------------|

### Energy storage

|                         |                             |
|-------------------------|-----------------------------|
| Number of battery slots | 2                           |
| Battery technology      | Lithium-Ion (Smart battery) |

### Interfaces

|            |                                       |
|------------|---------------------------------------|
| Interfaces | 2x USB 3.0                            |
|            | 1x USB 3.0 inset                      |
|            | WLAN 802.11 a/g/n                     |
|            | Bluetooth 4.0 Class 1+2               |
| Network    | 1 x Ethernet (10/100/1000 Mbps), RJ45 |

### Dimensions

|                    |                                       |
|--------------------|---------------------------------------|
| Width              | 356 mm                                |
| Height             | 262 mm                                |
| Depth              | 42 mm                                 |
| Note on dimensions | 73 mm with folded-out supporting feet |

#### External dimensions

# ITC 8113 GSK 02 - Tablet PC



2403267

<https://www.phoenixcontact.com/us/products/2403267>

|                        |   |
|------------------------|---|
| Width / Height / Depth | 356 mm / 262 mm / 42 mm (73 mm with folded-out supporting feet) |
|------------------------|---|

## Environmental and real-life conditions

### Ambient conditions

|  |                                |
|--|--------------------------------|
| Degree of protection                     | IP53                           |
| Ambient temperature (operation)          | 0 °C ... 40 °C                 |
| Permissible humidity (operation)         | 10 % ... 85 % (non-condensing) |
| Permissible humidity (storage/transport) | 10 % ... 85 % (non-condensing) |

## Mounting

|               |                    |
|---------------|--------------------|
| Mounting type | Mobile application |
|---------------|--------------------|

# ITC 8113 GSK 02 - Tablet PC

2403267

<https://www.phoenixcontact.com/us/products/2403267>



## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43211509 |
|-------------|----------|

# ITC 8113 GSK 02 - Tablet PC



2403267

<https://www.phoenixcontact.com/us/products/2403267>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)