

ITC 8113 PORTREPLICATOR - Holder



2403313

<https://www.phoenixcontact.com/us/products/2403313>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rotatable/tiltable port replicator (without lock) for ITC 8113 xxx with 1x Ethernet (10/100/1000 Mbit) RJ45 and 4x USB 2.0.

Commercial data

Item number	2403313
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRBBAZ
GTIN	4055626283449
Weight per piece (including packing)	500 g
Weight per piece (excluding packing)	2,701 g
Country of origin	DE

ITC 8113 PORTREPLICATOR - Holder



2403313

<https://www.phoenixcontact.com/us/products/2403313>

Technical data

Product properties

Product type	Assembly element
--------------	------------------

Electrical properties

Supply

Supply voltage	20 V DC (Via ITC8113 power supply unit (power supply unit not included))
----------------	--

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 40 °C
---------------------------------	----------------

Mounting

Mounting type	Vesa MIS-D, 75 and 100
---------------	------------------------

ITC 8113 PORTREPLICATOR - Holder



2403313

<https://www.phoenixcontact.com/us/products/2403313>

Classifications

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

ITC 8113 PORTREPLICATOR - Holder



2403313

<https://www.phoenixcontact.com/us/products/2403313>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com