


OFFICE-DEMO-PC - Building management system



2404321

<https://www.phoenixcontact.com/us/products/2404321>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Emalytics Supervisor demo license for testing and engineering purposes with unlimited functionality and 12-month validity, which will be renewed annually.

This license is not approved for use in production systems.

Licenses for use in production systems are available separately.

Please note: By using the demo license, the server used will be bound to the demo license for the long term. Productive operation is no longer possible for a server licensed for demo purposes. That is why we recommend using a dedicated server for internal test purposes.

powered by

niagara
framework®

Commercial data

Item number	2404321
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR18
Product key	DRHBAA
GTIN	4055626364711
Weight per piece (including packing)	0.001 MGM
Weight per piece (excluding packing)	0.001 MGM
Customs tariff number	49119900
Country of origin	US

Technical data

Notes

Note on application	This license is not approved for use in production systems. Licenses for use in production systems are available separately.
Note on application	By using the demo license, the controller used will be bound to the demo license for the long term. Productive operation is no longer possible for a controller licensed for demo purposes. That is why we recommend using a dedicated controller for internal testing purposes.

Product properties

Product type	Building management system
Area of application	Building technology

System properties

Type of software	On-premises
Intended use for the software	Automation

License information

Type of license	Demo license
License duration	not relevant

Functionality

Integrated function	Analysis
	Data acquisition
	Diagnostics
	Startup
	Communication
	Configuration
	Project planning
	Simulation
Target system	Server
Number of data points	not relevant
Number of clients	nicht relevant

System requirements

Operating system	Windows® 10
	Windows® 8.1 Enterprise (64-Bit)
	Windows® Server 2012 Standard
	Windows® Server 2012 R2 Standard
Hard disk memory	min. 4 GByte (more recommended depending on the archiving requirements)
Interfaces	1 x Ethernet (10/100 Mbps), RJ45
Languages supported	German, English
Screen resolution	1024 x 768 pixel(s) ,or higher

2404321

<https://www.phoenixcontact.com/us/products/2404321>

Classifications

ECLASS

ECLASS-13.0	27242590
ECLASS-15.0	27242590

ETIM

ETIM 10.0	EC001435
-----------	----------

UNSPSC

UNSPSC 21.0	43233600
-------------	----------

2404321

<https://www.phoenixcontact.com/us/products/2404321>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com