

VISU+ 2 SP IEC 61850 - Visualization software



2404835

<https://www.phoenixcontact.com/us/products/2404835>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Driver license for IEC 61850 MMS Client. Only in conjunction with a valid Visu+ runtime license including driver connection (Visu+ RT-D).

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2404835 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | DRDADG |
| GTIN | 4055626457789 |
| Weight per piece (including packing) | 102.5 g |
| Weight per piece (excluding packing) | 102.5 g |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Visualization |
|--------------|---------------|

System properties

| | |
|-------------------------------|---------------|
| Intended use for the software | Visualization |
|-------------------------------|---------------|

License information

| | |
|-----------------|----------------|
| Type of license | Driver license |
|-----------------|----------------|

Functionality

| | |
|---------------------|--|
| Basic functions | Connection as IEC 61850 MMS client to all IEC 61850 MMS servers. |
| Number of I/O nodes | 0 |

System requirements

| | |
|-----------------------------|---|
| Operating equipment | Keyboard, mouse |
| Operating system | Windows® XP (SP3) |
| | Windows® Vista Business |
| | Windows® 7 Professional SP1 (32-Bit/64-Bit) |
| | Windows® 7 Ultimate SP1 (32-Bit/64-Bit) |
| | Windows® 8 Professional (32-Bit/64-Bit) |
| | Windows® 8 Enterprise (32-Bit/64-Bit) |
| | Windows® Server 2003 |
| | Windows® Server 2008 |
| Windows® Server 2008 R2 | |
| Windows® 10 (32-Bit/64-Bit) | |
| Hard disk memory | min. 1 GByte (recommended: 2 GB) |
| Supported browsers | Internet Explorer 5.5 or higher |
| Languages supported | German, English, French, Italian |
| Screen resolution | 1024 x 768 pixel(s) (XGA) |

2404835

<https://www.phoenixcontact.com/us/products/2404835>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242502 |
| ECLASS-15.0 | 27242502 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001416 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43231500 |
|-------------|----------|

2404835

<https://www.phoenixcontact.com/us/products/2404835>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com