

UM 72-FE KMGY - Foot element



2695840

<https://www.phoenixcontact.com/us/products/2695840>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Base element for the DIN rail, for mounting below UM-PRO PROFILE (width: 72 mm), Foot element



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2695840 |
| Packing unit | 10 pc |
| Minimum order quantity | 20 pc |
| Product key | ACHDBA |
| GTIN | 4046356479592 |
| Weight per piece (including packing) | 5.91 g |
| Weight per piece (excluding packing) | 5.89 g |
| Country of origin | PL |

UM 72-FE KMGY - Foot element



2695840

<https://www.phoenixcontact.com/us/products/2695840>

Technical data

Product properties

| | |
|----------------|------------------------------|
| Product type | Base latches |
| Housing type | Press-drawn section housings |
| Housing series | UM |
| Product family | UM72 |

Material specifications

| | |
|--|-----------------------|
| Color (Housing) | light gray (RAL 7035) |
| Material Housing | PA |
| Flammability rating according to UL 94 | V0 |

UM 72-FE KMGY - Foot element



2695840

<https://www.phoenixcontact.com/us/products/2695840>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2695840>



UL Recognized

Approval ID: E240868

UM 72-FE KMGY - Foot element



2695840

<https://www.phoenixcontact.com/us/products/2695840>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UM 72-FE KMGY - Foot element



2695840

<https://www.phoenixcontact.com/us/products/2695840>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com