

FL MGUARD SMART/533 VPN - Router



2700181

<https://www.phoenixcontact.com/us/products/2700181>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Router with intelligent Firewall, Stateful Inspection Firewall for optimum safety and extremely simple configuration, VPN as per IPsec standard, hardware encryption with up to 70 Mbps, in the portable housing, power supply via USB, 533-MHz processor cycle frequency

Commercial data

Item number	2700181
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DNN333
GTIN	4046356498074
Weight per piece (including packing)	218.3 g
Weight per piece (excluding packing)	218.3 g
Customs tariff number	85176200
Country of origin	DE

2700181

<https://www.phoenixcontact.com/us/products/2700181>

Technical data

Dimensions

Width	77 mm
Height	27 mm
Depth	115 mm

Interfaces

Ethernet

Connection method	RJ45
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
No. of channels	2

System properties

System requirements

Supported browsers	HTTPS support required
--------------------	------------------------

Product properties

Product type	Security routers without DIN rail mounting
--------------	--

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Electrical properties

Local diagnostics	1 (PC) Link status/LAN data transmission Green LED
	3 (Internet) Link status/WAN data transmission Green LED
	2 (heartbeat) Device function Red/green LED

Supply

Supply voltage	5 V DC (from USB interface)
Power supply connection	via USB interface

Connection data

Connection method	RJ45, shielded
-------------------	----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

FL MGUARD SMART/533 VPN - Router



2700181

<https://www.phoenixcontact.com/us/products/2700181>

Permissible humidity (operation)	20 % ... 90 % (non-condensing)
----------------------------------	--------------------------------

FL MGuard SMART/533 VPN - Router



2700181

<https://www.phoenixcontact.com/us/products/2700181>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com