

FL RUGGED BOX DIR-1 - Control box



2701440

<https://www.phoenixcontact.com/us/products/2701440>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Control box set for constructing wireless systems for industrial applications, incl. panel antenna and 3 m antenna cable for 2.4/5 GHz, IP66, with DIN rail, plugs, and screw connections, with 100 V ... 240 V power supply unit, without devices

Commercial data

Item number	2701440
Packing unit	1 pc
Sales key	DN23
Product key	DNN2WZ
GTIN	4046356752206
Weight per piece (including packing)	1.969 kg
Weight per piece (excluding packing)	1.969 kg
Customs tariff number	85177100
Country of origin	DE

FL RUGGED BOX DIR-1 - Control box

2701440

<https://www.phoenixcontact.com/us/products/2701440>

Set consists of

ANT-DIR-2459-01 - Antenna

2701186

<https://www.phoenixcontact.com/us/products/2701186>

Directional antenna for wall or mast mounting, 2.4 GHz / 5 GHz, gain: 9 dBi, degree of protection: IP67, shockproof: IK06, saltwater-resistant, connection: N (female), incl. mounting bracket and mast clamps, ATEX and IECEx approval



RAD-PIG-RSMA/N-3 - Coaxial cable

2903266

<https://www.phoenixcontact.com/us/products/2903266>

Antenna cable, outside diameter: 5 mm, inner conductor: rigid, attenuation: 1.2/2.0/3.0 dB at 0.9/2.4/5.8 GHz, connection: N (male) -> RSMA (male), cable length: 3 m, technically improved, lead-free successor item available: item number 1340136



FL RUGGED BOX DIR-1 - Control box

2701440

<https://www.phoenixcontact.com/us/products/2701440>



STEP-PS/ 1AC/24DC/0.5 - Power supply

2868596

<https://www.phoenixcontact.com/us/products/2868596>




Primary-switched STEP POWER power supply for DIN rail and direct mounting, input: 1-phase, output: 24 V DC/0.5 A

PT 2,5-QUATTRO - Feed-through terminal block

3209578

<https://www.phoenixcontact.com/us/products/3209578>



Feed-through terminal block, nom. voltage: 800 V, nominal current: 24 A, number of connections: 4, connection method: Push-in connection, Rated cross section: 2.5 mm², cross section: 0.14 mm² - 4 mm², mounting type: NS 35/7,5, NS 35/15, color: gray

FL RUGGED BOX DIR-1 - Control box

2701440


<https://www.phoenixcontact.com/us/products/2701440>



PT 2,5-QUATTRO BU - Feed-through terminal block

3209581

<https://www.phoenixcontact.com/us/products/3209581>




Feed-through terminal block, nom. voltage: 800 V, nominal current: 24 A, number of connections: 4, connection method: Push-in connection, Rated cross section: 2.5 mm², cross section: 0.14 mm² - 4 mm², mounting type: NS 35/7,5, NS 35/15, color: blue

PT 2,5-QUATTRO-PE - Protective conductor terminal block

3209594

<https://www.phoenixcontact.com/us/products/3209594>



Protective conductor terminal block, number of connections: 4, connection method: Push-in connection, Rated cross section: 2.5 mm², cross section: 0.14 mm² - 4 mm², mounting type: NS 35/7,5, NS 35/15, color: green-yellow

FL RUGGED BOX DIR-1 - Control box

2701440

<https://www.phoenixcontact.com/us/products/2701440>



VS-08-RJ45-5-Q/IP20 - RJ45 connector

1656725

<https://www.phoenixcontact.com/us/products/1656725>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5, material: Plastic, connection method: Insulation displacement connection, connection cross section: AWG 26- 23, cable outlet: straight, color: traffic gray A RAL 7042, Ethernet

FL RUGGED BOX DIR-1 - Control box



2701440

<https://www.phoenixcontact.com/us/products/2701440>

Technical data

Product properties

Product type	Control box
--------------	-------------

Dimensions

Width	174 mm
Height	254 mm
Depth	137 mm

Material specifications

Housing material	PC
------------------	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
----------------------	------

FL RUGGED BOX DIR-1 - Control box



2701440

<https://www.phoenixcontact.com/us/products/2701440>

Classifications

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

FL RUGGED BOX DIR-1 - Control box



2701440

<https://www.phoenixcontact.com/us/products/2701440>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(b)-II, 6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d16ccbe4-5be1-47f1-8915-b94d7ccba961

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com