

ME DH 27 NS 35 KMGY - Spacer

2706289

<https://www.phoenixcontact.com/us/products/2706289>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Spacer, for protecting the input and output contacts for NS 35 DIN rails



Your advantages

- Easy installation

Commercial data

Item number	2706289
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ACHACZ
GTIN	4046356517492
Weight per piece (including packing)	10.754 g
Weight per piece (excluding packing)	9.4 g
Country of origin	DE

ME DH 27 NS 35 KMGY - Spacer



2706289

<https://www.phoenixcontact.com/us/products/2706289>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	-----------------------------------------------------------

Product properties

Product type	Mounting material
Housing type	DIN rail housing
Housing series	ME
Ventilation openings present	no

Dimensions

Width	30.5 mm
Height	88 mm
Depth	22.8 mm

Material specifications

Color (Housing)	light gray (RAL 7035)
Flammability rating according to UL 94	V0
Housing material	PA

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

ME DH 27 NS 35 KMGY - Spacer



2706289

<https://www.phoenixcontact.com/us/products/2706289>

Classifications

ECLASS

ECLASS-13.0

27190605

ETIM

ETIM 9.0

EC002779

UNSPSC

UNSPSC 21.0

31261500

ME DH 27 NS 35 KMGY - Spacer



2706289

<https://www.phoenixcontact.com/us/products/2706289>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com