

UM122-SEMFE-A92 KMGY - Lateral element



2706593

<https://www.phoenixcontact.com/us/products/2706593>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Lateral element with screw fixture to attach profile cover, for assembly on NS 35/7.5



Commercial data

Item number	2706593
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDBA
GTIN	4017918826796
Weight per piece (including packing)	29.59 g
Weight per piece (excluding packing)	28.9 g
Customs tariff number	39269097
Country of origin	PL

UM122-SEMFE-A92 KMGY - Lateral element



2706593

<https://www.phoenixcontact.com/us/products/2706593>

Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM122
Ventilation openings present	no

Dimensions

Depth	127.5 mm
-------	----------

Material specifications

Color (Side element)	light gray (RAL 7035)
Material Lateral element	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

UM122-SEMFE-A92 KMGY - Lateral element



2706593

<https://www.phoenixcontact.com/us/products/2706593>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2706593>



UL Recognized

Approval ID: E240868

UM122-SEMFE-A92 KMGY - Lateral element



2706593

<https://www.phoenixcontact.com/us/products/2706593>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM122-SEMFE-A92 KMGY - Lateral element



2706593

<https://www.phoenixcontact.com/us/products/2706593>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.19 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com