

EG 45-G/ABS GN S75 - Mounting base housing

2706836

<https://www.phoenixcontact.com/us/products/2706836>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mounting base housing ,Component housing, length: 75 mm, Lower part, color: green, width: 45 mm, height: 107.5 mm

The figure shows a fully mounted version of the electronic housing

Commercial data

Item number	2706836
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	ACHCGA
GTIN	4017918842772
Weight per piece (including packing)	55.45 g
Weight per piece (excluding packing)	54.358 g
Country of origin	DE

EG 45-G/ABS GN S75 - Mounting base housing



2706836

<https://www.phoenixcontact.com/us/products/2706836>

Technical data

Product properties

Housing type	Component housing
Number of positions	16

Dimensions

Width	45 mm
Installed height	107.5 mm
Height NS 35/7,5	107.5 mm
Depth	75 mm
Length	75 mm

Material specifications

Color	green
Flammability rating according to UL 94	HB
Housing material	Acryl butadiene styrene (ABS)

EG 45-G/ABS GN S75 - Mounting base housing



2706836

<https://www.phoenixcontact.com/us/products/2706836>

Classifications

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

EG 45-G/ABS GN S75 - Mounting base housing



2706836

<https://www.phoenixcontact.com/us/products/2706836>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com