

ME MAX 17,5 PLATE GY - Insertion plate



2707291

<https://www.phoenixcontact.com/us/products/2707291>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Insertion plate, width: 14.2 mm, height: 73.6 mm, depth: 1 mm, color: gray (similar RAL 7042)

Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2707291 |
| Packing unit | 200 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | ACHABZ |
| GTIN | 4017918897604 |
| Weight per piece (including packing) | 1.22 g |
| Weight per piece (excluding packing) | 1.195 g |
| Country of origin | DE |

ME MAX 17,5 PLATE GY - Insertion plate



2707291

<https://www.phoenixcontact.com/us/products/2707291>

Technical data

Notes

| | |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

Product properties

| | |
|------------------------------|------------------|
| Product type | Cover |
| Housing type | DIN rail housing |
| Housing series | ME-MAX |
| Ventilation openings present | no |

Dimensions

| | |
|--------|---------|
| Width | 14.2 mm |
| Height | 73.6 mm |
| Depth | 1 mm |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| CTI according to IEC 60112 | 600 |
| Housing material | PA |

Mounting

| | |
|---------------|------|
| Mounting type | Slot |
|---------------|------|

ME MAX 17,5 PLATE GY - Insertion plate



2707291

<https://www.phoenixcontact.com/us/products/2707291>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261501 |
|-------------|----------|

ME MAX 17,5 PLATE GY - Insertion plate



2707291

<https://www.phoenixcontact.com/us/products/2707291>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com