

# EB 10- DIK GY - Insertion bridge



2715937

<https://www.phoenixcontact.com/us/products/2715937>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, pitch: 6.15 mm, number of positions: 10, color: gray



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2715937       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BE19          |
| Product key                          | BE1Z2X        |
| GTIN                                 | 4017918061685 |
| Weight per piece (including packing) | 4.4 g         |
| Weight per piece (excluding packing) | 4.266 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | PL            |

# EB 10- DIK GY - Insertion bridge



2715937

<https://www.phoenixcontact.com/us/products/2715937>

## Technical data

### Product properties

|                     |                  |
|---------------------|------------------|
| Product type        | Insertion bridge |
| Number of positions | 10               |
| Pitch               | 6.15 mm          |
| Potentials          | 10               |

### Dimensions

|       |         |
|-------|---------|
| Pitch | 6.15 mm |
|-------|---------|

### Material specifications

|                     |                 |
|---------------------|-----------------|
| Color               | gray (RAL 7042) |
| Material            | Copper          |
| Insulating material | PA              |

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

# EB 10- DIK GY - Insertion bridge



2715937

<https://www.phoenixcontact.com/us/products/2715937>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000489 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# EB 10- DIK GY - Insertion bridge



2715937

<https://www.phoenixcontact.com/us/products/2715937>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.044 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)