

# IBS PCWORX E - Programming software



2729415

<https://www.phoenixcontact.com/us/products/2729415>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IBS PC WORX, software package without license, only 40 I/O points, English. PC WORX 2.x software is licensed by means of a license file. This can be downloaded.

## Commercial data

Item number	2729415
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR13
Product key	DRDBAC
GTIN	4017918169350
Weight per piece (including packing)	469.6 g
Weight per piece (excluding packing)	469.6 g
Customs tariff number	85234945
Country of origin	DE

## Technical data

### Product properties

Product type	Programming
Scope of supply	Software package: 1x software on CD, 1x Quick Start Guide - PC WORX licenses: 1 x license on floppy disk, 1 x emergency disk, 1 x registration, - user manuals

### System properties

Control system	(Target system) Field controllers, Remote Field Controllers
Intended use for the software	Programming

### Functionality

Basic functions	Planning an automation system
	Parameterizing the INTERBUS devices
	Operation and display of INTERBUS
	Programming an automation system in accordance with IEC 61131-3
	Communication in accordance with IEC 61131-5
	IEC 61131 includes the following programming languages: - Instruction list (IL), -Function block diagram (FBD), -Ladder diagram (LD), -Structured text (ST), -Symbolic flowchart (SFC)
Add-on to IEC 61131: MSFC (with license IBS PCWORX PRO-MSFC LIC 2729512 only)	
Programming languages supported	Programming in acc. with IEC 61131-3
Configuration	INTERBUS
Diagnostics	INTERBUS
Control system	(Target system) Field controllers, Remote Field Controllers
Associated hardware	Phoenix Contact control
Supported controllers	Field controllers and Remote Field Controllers

### System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows NT 4.0, Windows 2000
Processor	Min. Pentium 100 MHz (Pentium II 266 MHz or higher recommended)
Hard disk memory	124.99780654907 Mbyte
Interfaces	1 x parallel, 1 x serial
Languages supported	English
Optical drive	CD-ROM
Disk drive	yes
Screen resolution	640 x 480

2729415

<https://www.phoenixcontact.com/us/products/2729415>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)