

IB L2 BOX TEMP 2/2 M12 - I/O module



2731924

<https://www.phoenixcontact.com/us/products/2731924>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Analog input module, 2 analog inputs, RTD, TC, 2-, 3-, and 4-conductor sensors, 2-conductor connection technology, IP65/IP67 degree of protection

Product description

Like their digital counterparts, the analog input modules have also been designed with IP67 protection and for use directly on the machine. They allow nearly all analog standard signals that are used in mechanical engineering to be linked to INTERBUS.

The two-channel analog input module can detect voltage and current signals (0 - 10 V, 0 - 20 mA, 4 - 20 mA) and process them with a resolution of 12 bits.

Another module is designed for the detection of temperatures. All conventional resistance thermometers (RTD) and thermocouples (TC) can be connected to this module. The module also has two channels and a resolution of 16 bits.

All analog sensors are connected with common M12 connectors. The module is linked to INTERBUS Loop 2 like the supply voltage, using the QUICKON fast connection system.

Commercial data

Item number	2731924
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN16
Product key	DRIA34
GTIN	4017918171414
Weight per piece (including packing)	199.5 g
Weight per piece (excluding packing)	156.94 g
Customs tariff number	85371099
Country of origin	DE

IB L2 BOX TEMP 2/2 M12 - I/O module



2731924

<https://www.phoenixcontact.com/us/products/2731924>

Technical data

Electrical properties

Test section	Bus/FE 500 V AC 50 Hz 1 min
	FE/Inputs 500 V AC 50 Hz 1 min

Supply


I/O voltage	24 V DC (via INTERBUS-Loop 2)
I/O voltage range	19.2 V DC ... 30 V DC
Residual ripple	± 1.2 V DC
Typical current consumption	45 mA (from INTERBUS-Loop 2)

Interfaces

INTERBUS-Loop 2

Connection method	QUICKON fast connection
-------------------	-------------------------

Dimensions

Dimensional drawing	
Width	62 mm
Height	60 mm
Length	95 mm

IB L2 BOX TEMP 2/2 M12 - I/O module




2731924

<https://www.phoenixcontact.com/us/products/2731924>

Drawings

Dimensional drawing




IB L2 BOX TEMP 2/2 M12 - I/O module



2731924

<https://www.phoenixcontact.com/us/products/2731924>

Connection diagram



IB L2 BOX TEMP 2/2 M12 - I/O module



2731924

<https://www.phoenixcontact.com/us/products/2731924>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com