

ASI IO ME DI 4 AB - Distributed I/O device



2741671

<https://www.phoenixcontact.com/us/products/2741671>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Digital input/output module, degree of protection IP20, 4 digital inputs, 24 V DC, COMBICON plugs included

Your advantages

- COMBICON connection technology for the I/Os
- COMBICON connection technology for AS-Interface
- Overall width: 12.5 mm
- Optimized for DIN rail mounting

Commercial data

Item number	2741671
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR03
Product key	DRI631
GTIN	4017918915278
Weight per piece (including packing)	147.57 g
Weight per piece (excluding packing)	147.57 g
Customs tariff number	85176200
Country of origin	SG

ASI IO ME DI 4 AB - Distributed I/O device



2741671

<https://www.phoenixcontact.com/us/products/2741671>

Technical data

Dimensions

Width	22.5 mm
Height	102 mm
Depth	105 mm

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Material specifications

Color	green
-------	-------

Interfaces

AS-Interface

Connection method	COMBICON connectors
Designation connection point	AS-i
Number of positions	2
Transmission speed	167 kbps

System properties

Programming data

ID code (dec.)	10
----------------	----

Input data

Digital:

Input name	Digital inputs
Number of inputs	4
Connection method	COMBICON connectors
Connection technology	2-, 3-conductor

Product properties

Product type	I/O component
Product family	AS-i
Type	Block design
Mounting position	any
No. of channels	4

Connection data

Connection method	COMBICON connectors
-------------------	---------------------

ASI IO ME DI 4 AB - Distributed I/O device



2741671

<https://www.phoenixcontact.com/us/products/2741671>

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Degree of protection	IP20
Ambient temperature (storage/transport)	-25 °C ... 85 °C

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail: 35 mm
	DIN rail mounting
Mounting position	any

ASI IO ME DI 4 AB - Distributed I/O device



2741671

<https://www.phoenixcontact.com/us/products/2741671>

Classifications

UNSPSC

UNSPSC 21.0	32151602
-------------	----------

2741671

<https://www.phoenixcontact.com/us/products/2741671>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com