

FL CAT5 FLEX CONF/ - Network cable



2744843

<https://www.phoenixcontact.com/us/products/2744843>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CAT5-SF/UTP cable (J-LI02YS(ST)C H 2 x 2 x 26 AWG), light-duty, flexible installation cable 2 x 2 x 0.14 mm², stranded, shielded, outer sheath: 5.75 mm ± 0.15 mm diameter, preassembled on both sides with RJ45 plug, crossover or line assignment

FL CAT5 HEAVY

Commercial data

Item number	2744843
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB50
Product key	ABNABG
Weight per piece (excluding packing)	19.8 g
Customs tariff number	85444993
Country of origin	DE

Technical data

Product properties

Product type	Data cable preassembled
Product family	RJ45 STANDARD CAT5
Application	Flexible installation
Number of positions	4
Connection profile	RJ45

Electrical properties

Transmission medium	Copper
Transmission speed	100 Mbps
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps
Wave impedance	100 Ω

Mechanical properties

Tensile strength short-term/long-term	50N bei Installation / 10N nach Installation
---------------------------------------	--

Material specifications

Flammability rating according to UL 94	V0
Outer sheath, material	Plastic

Dimensions

External dimensions

External diameter min.	5.6 mm
External diameter max.	5.9 mm

Cable/line

Cable weight	43.00 kg/km
Cable abbreviation	J-LI02YS(ST) CH 2 x 2 x 26 AWG
Outer sheath, material	Plastic
External sheath, color	water blue RAL 5021
Single wire, material	Foam skin (polyethylene)
Individual wire diameter	1 mm (wires to pairs, pairs are arranged to form a cable core)
Single wire, cross section	0.14 mm ²
Single wire, color	white/orange-orange (pair 1)
Wave impedance	100 Ω ±15 %
Loop resistance	≤ 284.00 Ω/km
Working capacitance	48 nF (per kilometer)
Smallest bending radius, fixed installation	30 mm
Tensile strength short-term/long-term	50N bei Installation / 10N nach Installation

FL CAT5 FLEX CONF/ - Network cable



2744843

<https://www.phoenixcontact.com/us/products/2744843>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2744843>



EAC

Approval ID: 19060508

FL CAT5 FLEX CONF/ - Network cable



2744843

<https://www.phoenixcontact.com/us/products/2744843>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

FL CAT5 FLEX CONF/ - Network cable



2744843

<https://www.phoenixcontact.com/us/products/2744843>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com