

# IBS STME 24 BK RB-T - Replacement electronics module



2752932

<https://www.phoenixcontact.com/us/products/2752932>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement module electronics for IBS ST (ZF) 24 BK RB-T



The photo shows the complete module

## Your advantages

- Copper or fiber optic connection
- Additional remote/local bus branches
- Additional I/Os onboard

## Commercial data

Item number	2752932
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR03
Product key	DRI311
GTIN	4017918108618
Weight per piece (including packing)	343.2 g
Weight per piece (excluding packing)	252.74 g
Customs tariff number	85389091
Country of origin	DE

# IBS STME 24 BK RB-T - Replacement electronics module



2752932

<https://www.phoenixcontact.com/us/products/2752932>

## Technical data

### Interfaces

#### INTERBUS

Connection method	9-pos. D-SUB plug/socket
Designation connection point	Incoming/Outgoing Remote Bus
Number of positions	9

#### ST local bus

Transmission speed	500 kbps
--------------------	----------

#### INTERBUS

Connection method	9-pos. D-SUB socket
Number of positions	9

### Input data

#### Digital:

Connection technology	Screw connection
-----------------------	------------------

### Product properties

Product type	I/O component
Product family	Smart Terminal ST
Type	modular
	INTERBUS Smart Terminal

### Connection data

Connection method	Screw connection
Stripping length	8 mm

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
----------------------	------

# IBS STME 24 BK RB-T - Replacement electronics module



2752932

<https://www.phoenixcontact.com/us/products/2752932>

## Classifications

### ECLASS

ECLASS-13.0	27242604
ECLASS-15.0	27242604

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# IBS STME 24 BK RB-T - Replacement electronics module



2752932

<https://www.phoenixcontact.com/us/products/2752932>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)