

IBS IP CDI 3/24-F - I/O module



2753203

<https://www.phoenixcontact.com/us/products/2753203>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS input/output module, 8 digital inputs, supply voltage: 24 V DC, protection type: IP65,
-Installation remote bus devices (5-pos. initiator connectors)

Commercial data

Item number	2753203
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN16
Product key	DRIA53
GTIN	4017918099541
Weight per piece (including packing)	954.2 g
Weight per piece (excluding packing)	9.27 g
Customs tariff number	85389091
Country of origin	DE

Technical data

Product properties

Number of plugs	8
-----------------	---

Electrical properties

Supply

Supply voltage	24 V DC
Supply voltage range	20 V DC ... 30 V DC (including ripple)
Residual ripple	3.6 V _{PP}
Typical current consumption	175 mA (plus power supply for sensors)

Input data

Digital

Connection technology	4-conductor
Typical input current per channel	7 mA

Dimensions

Width	175 mm
Height	80 mm
Length	60 mm

Material specifications

Color	red
-------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
----------------------	------

IBS IP CDI 3/24-F - I/O module

2753203

<https://www.phoenixcontact.com/us/products/2753203>



Environmental product compliance

China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com