

EG 90-GP/ABS GN - Mounting base housing

2764315

<https://www.phoenixcontact.com/us/products/2764315>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component housing, Lower housing part, with snap-on foot and test opening with side cover, without vents, width: 90 mm, height: 75 mm, color: green (similar RAL 6021), cross connection: without bus connector, number of positions cross connector: not relevant

The figure shows a fully mounted version of the electronic housing

Your advantages

- Tool-free mounting

Commercial data


Item number	2764315
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC11
Product key	ACHCGA
GTIN	4017918065942
Weight per piece (including packing)	88.3 g
Weight per piece (excluding packing)	68.598 g
Customs tariff number	85389099
Country of origin	PL

Technical data

Product properties

Product type	Lower housing part
Housing type	Component housing
Housing series	EG
Product family	EG...G
Type	Lower housing parts with test opening with side cover, housing cover necessary to complete the module
Number of positions	34
Max. number of positions	0)
Ventilation openings present	no

Dimensions

Dimensional drawing	
Width	90 mm
Height	75 mm

PCB design

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

Material specifications

Color (Housing)	green (RAL 6021)
Flammability rating according to UL 94	HB

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 80 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 80 °C

PCB data

Thickness of the PCB	1.4 mm ... 1.8 mm
----------------------	-------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

EG 90-GP/ABS GN - Mounting base housing


2764315

<https://www.phoenixcontact.com/us/products/2764315>



Drawings

Dimensional drawing



EG 90-GP/ABS GN - Mounting base housing

2764315

<https://www.phoenixcontact.com/us/products/2764315>



Component mounting side, if the double-level upper part is used

EG 90-GP/ABS GN - Mounting base housing

2764315

<https://www.phoenixcontact.com/us/products/2764315>



valid for PCB 1; 2; 3; 4; 5 und 6, see explosion drawing



valid for PCB 7; 8; 11 and 12, see explosion drawing

EG 90-GP/ABS GN - Mounting base housing

2764315

<https://www.phoenixcontact.com/us/products/2764315>



valid for PCB 9 and 10, see explosion drawing

EG 90-GP/ABS GN - Mounting base housing

2764315

<https://www.phoenixcontact.com/us/products/2764315>



valid for PCB 13

EG 90-GP/ABS GN - Mounting base housing

2764315

<https://www.phoenixcontact.com/us/products/2764315>



valid for PCB 14

EG 90-GP/ABS GN - Mounting base housing



2764315

<https://www.phoenixcontact.com/us/products/2764315>

Classifications

ECLASS

ECLASS-13.0	27190601
-------------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

EG 90-GP/ABS GN - Mounting base housing



2764315

<https://www.phoenixcontact.com/us/products/2764315>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com