

IBS AI 3 - I/O module



2767192

<https://www.phoenixcontact.com/us/products/2767192>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2767192 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DN16 |
| Product key | DRIAB1 |
| GTIN | 4017918067014 |
| Weight per piece (including packing) | 884.3 g |
| Weight per piece (excluding packing) | 8.56 g |
| Customs tariff number | 85389091 |
| Country of origin | DE |

Technical data

Interfaces

Local bus

| | |
|--------------------|----------|
| Bus system | INTERBUS |
| Transmission speed | 500 kbps |

Product properties

| | |
|--------------|---------------|
| Product type | I/O component |
| Type | modular |

Connection data

| | |
|-------------------|------------------|
| Connection method | Screw connection |
|-------------------|------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP20 |
|----------------------|------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Environmental product compliance

EU RoHS

| | |
|---|----------------------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(a), 6(a)-I, 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|