

# UEGM-SE 5 - Housing half shell

2792057

<https://www.phoenixcontact.com/us/products/2792057>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Side element for electronic housing UEGM ...

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2792057       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AC11          |
| Product key                          | ACHCCB        |
| GTIN                                 | 4017918349400 |
| Weight per piece (including packing) | 17.62 g       |
| Weight per piece (excluding packing) | 17 g          |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

# UEGM-SE 5 - Housing half shell



2792057

<https://www.phoenixcontact.com/us/products/2792057>

## Technical data

### Product properties

|                              |                     |
|------------------------------|---------------------|
| Product type                 | Housing half shells |
| Housing type                 | Component housing   |
| Housing type                 | Basic housing       |
| Housing series               | UEGM                |
| Product family               | UEGM                |
| Ventilation openings present | yes                 |

### Material specifications

|  |                  |
|--|------------------|
| Color (Housing)                        | green (RAL 6021) |
| Material                               | PA               |
| Flammability rating according to UL 94 | V0               |

### Environmental and real-life conditions

#### Ambient conditions

|   |  |
|---|--|
| Max. IP code to attain                  | IP20   |
| Ambient temperature (operation)         | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                   |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                   |

### Mounting

|               |         |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

# UEGM-SE 5 - Housing half shell



2792057

<https://www.phoenixcontact.com/us/products/2792057>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2792057>



**UL Recognized**

Approval ID: E240868

# UEGM-SE 5 - Housing half shell



2792057

<https://www.phoenixcontact.com/us/products/2792057>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190602 |
| ECLASS-15.0 | 27190602 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# UEGM-SE 5 - Housing half shell



2792057

<https://www.phoenixcontact.com/us/products/2792057>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)