

# PSM-SET-FSMA/4-HCS - FO connectors



2799487

<https://www.phoenixcontact.com/us/products/2799487>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

FO connectors, degree of protection: IP20, number of positions: 4, MM, material: Metal, connection method: Cable connection, cable outlet: straight



FSMA plugs

## Your advantages

- Suitable for quick and easy field assembly or repair
- Flexible application, thanks to reusable connector
- Outstanding transmission properties
- Ideal for PCF step-index (SI) fibers
- Robust design, thanks to F-SMA pin connector pattern
- No bonding or polishing

## Commercial data

Item number	2799487
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIAB
GTIN	4017918126742
Weight per piece (including packing)	37.9 g
Weight per piece (excluding packing)	37.06 g
Customs tariff number	85367000
Country of origin	DE

## Technical data

### Product properties

Product type	Fiber optic connector (cable side)
Type	FSMA
Number of positions	4
Cable outlet	straight

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Attenuation	≥ 2 dB (Insertion attenuation)
Transmission medium	FO
Transmission characteristics (category)	MM

### Connection data

Connection method	Cable connection
-------------------	------------------

### Dimensions

Width	8.1 mm
Length	83 mm

### Mechanical characteristics

Ferrule diameter	3.20 mm
------------------	---------

### Material specifications

Material	Metal
Housing material	Metal

### Cable/line

Cable type	PCF 200/230
Cable type	Single wires
External cable diameter	2.9 mm ... 2.9 mm
Individual wire diameter	2.9 mm

### FO cable

Fiber	200/230 μm
Fiber type	PCF
Transmission medium	FO

### Characteristics

Attenuation	≥ 2 dB (Insertion attenuation)
-------------	--------------------------------

### Environmental and real-life conditions

# PSM-SET-FSMA/4-HCS - FO connectors



2799487

<https://www.phoenixcontact.com/us/products/2799487>

## Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Ambient temperature (assembly)	0 °C ... 50 °C

## Mounting

Mounting type	For field assembly
cable layer type	Indoors

2799487

<https://www.phoenixcontact.com/us/products/2799487>

## Classifications

### ECLASS

ECLASS-13.0	19170122
ECLASS-15.0	19170122

### ETIM

ETIM 10.0	EC001122
-----------	----------

### UNSPSC

UNSPSC 21.0	43223300
-------------	----------

2799487

<https://www.phoenixcontact.com/us/products/2799487>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	7.869 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)