

UPS-BAT-KIT-20X7AH - Uninterruptible power supply replacement battery



2800427

<https://www.phoenixcontact.com/us/products/2800427>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement battery for UPS-CP-BAT... energy storage



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2800427 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | CMURV9 |
| GTIN | 4046356551243 |
| Weight per piece (including packing) | 52,000 g |
| Weight per piece (excluding packing) | 52,000 g |
| Country of origin | CN |

UPS-BAT-KIT-20X7AH - Uninterruptible power supply replacement battery



2800427

<https://www.phoenixcontact.com/us/products/2800427>

Technical data

Energy storage

| | |
|------------------|---------------------------|
| Battery voltage | 12 V DC (per battery) |
| Charging voltage | 271.5 V DC ... 272.5 V DC |
| IQ technology | no |

Product properties

| | |
|---------------|---------|
| Product type | Battery |
| IQ technology | no |

Dimensions

| | |
|--------|-----------|
| Width | 65.00 mm |
| Height | 95.00 mm |
| Depth | 600.00 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|-----------------------------------------|----------------|
| Ambient temperature (operation) | 0 °C ... 40 °C |
| Ambient temperature (storage/transport) | 0 °C ... 45 °C |

UPS-BAT-KIT-20X7AH - Uninterruptible power supply replacement battery



2800427

<https://www.phoenixcontact.com/us/products/2800427>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26111710 |
|-------------|----------|

UPS-BAT-KIT-20X7AH - Uninterruptible power supply replacement battery



2800427

<https://www.phoenixcontact.com/us/products/2800427>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|-----------------------------------------|-------------------------------------------------------------------------------------|

China RoHS

| | |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-3 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com