

# BES 6-1N4007 - Component connector



2802552

<https://www.phoenixcontact.com/us/products/2802552>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component connector, pitch: 6 mm, number of positions: 1, color: gray, mounting type: Plug-in mounting

## Your advantages

- Is supplied as a set with two plug sockets

## Commercial data

Item number	2802552
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BE19
Product key	BE1Z3X
GTIN	4017918074470
Weight per piece (including packing)	7.8 g
Weight per piece (excluding packing)	7.8 g
Customs tariff number	85366990
Country of origin	PL

# BES 6-1N4007 - Component connector

2802552

<https://www.phoenixcontact.com/us/products/2802552>

## Technical data


### Product properties

Product type	Component plug terminal block
Number of positions	1
Pitch	6 mm

### Connection data

Tightening torque	0.5 ... 0.6 Nm
-------------------	----------------

### Dimensions

Dimensional drawing	
Pitch	6 mm

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Insulating material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Mounting

Mounting type	Plug-in mounting
---------------	------------------

# BES 6-1N4007 - Component connector


2802552

<https://www.phoenixcontact.com/us/products/2802552>



## Drawings

Dimensional drawing



# BES 6-1N4007 - Component connector



2802552

<https://www.phoenixcontact.com/us/products/2802552>

## Classifications

### ECLASS

ECLASS-13.0	27250305
ECLASS-15.0	27250305

### ETIM

ETIM 10.0	EC002018
-----------	----------

### UNSPSC

UNSPSC 21.0	39121600
-------------	----------

# BES 6-1N4007 - Component connector



2802552

<https://www.phoenixcontact.com/us/products/2802552>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6a892533-d3b2-4582-9104-7dc84ae31b11

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)