MPB 18/1-57 - Wiring bridge

2809238

https://www.phoenixcontact.com/us/products/2809238

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wiring bridge for modules with connecting pitch 17.5 mm, 1-phase, 57-pos.

Your advantages

- In combination with other devices in the distribution board, such as residual current devices and miniature circuit breakers
- Practical wiring of all common applications
- For combinations of lightning and surge arresters

Commercial data

Item number	2809238
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL18
Product key	CL132Z
GTIN	4017918076306
Weight per piece (including packing)	307.5 g
Weight per piece (excluding packing)	306 g
Customs tariff number	85369095
Country of origin	DE

Technical data

Product properties

Product type	Bridge
Type	Comb bridge
Number of positions	57

Electrical properties

Number of phases	1
Nominal current I_N	100 A

Material specifications

Color	gray (RAL 7042)
	copper color
Housing material	Plastic
Contact material	E-Cu 58

Classifications

ECLASS

ECLASS-15.0	27371306
ECLASS-13.0	27371306

ETIM

ETIM 10.0	EC000215

UNSPSC

UNSPSC 21.0	39121600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com