

IB L2-M BOX 24 DIO 4/4 BT - Operator terminal



2819273

<https://www.phoenixcontact.com/us/products/2819273>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pushbutton panel, operating buttons with LEDs, choice of decals for the buttons

Commercial data

Item number	2819273
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRIA63
GTIN	4017918877088
Weight per piece (including packing)	218.2 g
Weight per piece (excluding packing)	218.2 g
Customs tariff number	85389091
Country of origin	DE

Technical data

Electrical properties

Supply

Supply voltage	via INTERBUS-Loop 2
Supply voltage range	19.2 V DC ... 30 V DC
Residual ripple	±5 %
Max. current consumption	100 mA

Input data

Digital

Number of inputs	4
------------------	---

Output data

Digital

Number of outputs	4
-------------------	---

Connection data

Connection method	an M12 plug
-------------------	-------------

Dimensions

Width	26 mm
Height	26 mm
Length	139 mm

Material specifications

Color	green
-------	-------

IB L2-M BOX 24 DIO 4/4 BT - Operator terminal



2819273

<https://www.phoenixcontact.com/us/products/2819273>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com