

URELG 7-PMTK RD - Basic terminal block



2820990

<https://www.phoenixcontact.com/us/products/2820990>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Basic termination blocks, for coupling connectors, complete with end cover, color: red

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2820990 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | DK6115 |
| GTIN | 4017918076924 |
| Weight per piece (including packing) | 141.4 g |
| Weight per piece (excluding packing) | 140 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

URELG 7-PMTK RD - Basic terminal block



2820990

<https://www.phoenixcontact.com/us/products/2820990>

Technical data

Product properties

| | |
|---------------------|--------------|
| Product type | Relay socket |
| Number of positions | 7 |

Electrical properties

| | |
|-----------------------|--|
| Nominal voltage U_N | 400 V (voltage is determined by the coupling connector.) |
| Nominal current I_N | 16 A (current is determined by the coupling connector.) |

Connection data

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 7 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Dimensions

| | |
|-------|----------------------|
| Width | 45.6 mm (with cover) |
|-------|----------------------|

Material specifications

| | |
|---------------------|----------------|
| Color | red (RAL 3001) |
| Insulating material | PA |

URELG 7-PMTK RD - Basic terminal block



2820990

<https://www.phoenixcontact.com/us/products/2820990>

Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com