

URELG 7-PMTK RD - Basic terminal block



2820990

<https://www.phoenixcontact.com/us/products/2820990>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Basic termination blocks, for coupling connectors, complete with end cover, color: red

Commercial data

Item number	2820990
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DK6115
GTIN	4017918076924
Weight per piece (including packing)	141.4 g
Weight per piece (excluding packing)	140 g
Customs tariff number	85369010
Country of origin	DE

URELG 7-PMTK RD - Basic terminal block



2820990

<https://www.phoenixcontact.com/us/products/2820990>

Technical data

Product properties

Product type	Relay socket
Number of positions	7

Electrical properties

Nominal voltage U_N	400 V (voltage is determined by the coupling connector.)
Nominal current I_N	16 A (current is determined by the coupling connector.)

Connection data

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Width	45.6 mm (with cover)
-------	----------------------

Material specifications

Color	red (RAL 3001)
Insulating material	PA

URELG 7-PMTK RD - Basic terminal block



2820990

<https://www.phoenixcontact.com/us/products/2820990>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com