

PR2-BSC2/4X21 - Relay base



2833563

<https://www.phoenixcontact.com/us/products/2833563>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay base PR2-B, for industrial relay REL-IR with 2 or 4 changeover contacts, 2/2-level design, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

Your advantages

- Relay retaining bracket with labeling field and ejection function
- Plug-in input/interference suppression modules

Commercial data

Item number	2833563
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C463
Product key	DK6313
GTIN	4017918933791
Weight per piece (including packing)	70 g
Weight per piece (excluding packing)	62.96 g
Customs tariff number	85366990
Country of origin	CN

PR2-BSC2/4X21 - Relay base



2833563

<https://www.phoenixcontact.com/us/products/2833563>

Technical data

Product properties

Product type	Relay socket
--------------	--------------

Electrical properties

Nominal voltage U_N	300 V AC/DC
Nominal current I_N	12 A

Connection data

Input side

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ² 0.2 mm ² ... 1.5 mm ² (2 conductors with the same cross-section)
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ² 0.2 mm ² ... 1.5 mm ² (2 conductors with the same cross-section)
Conductor cross-section AWG	26 ... 14 26 ... 16 (2 conductors with the same cross-section)

Output side

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ² 0.2 mm ² ... 1.5 mm ² (2 conductors with the same cross-section)
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ² 0.2 mm ² ... 1.5 mm ² (2 conductors with the same cross-section)
Conductor cross-section AWG	26 ... 14 26 ... 16 (2 conductors with the same cross-section)

Dimensions

Width	27 mm
Height	75 mm
Depth Retaining bracket	84 mm (EL2-P35)

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C
---------------------------------	------------------

PR2-BSC2/4X21 - Relay base



2833563

<https://www.phoenixcontact.com/us/products/2833563>

Ambient temperature (storage/transport)	-25 °C ... 85 °C
---	------------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

PR2-BSC2/4X21 - Relay base

2833563

<https://www.phoenixcontact.com/us/products/2833563>



Classifications

UNSPSC

UNSPSC 21.0	39122335
-------------	----------

PR2-BSC2/4X21 - Relay base



2833563

<https://www.phoenixcontact.com/us/products/2833563>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com