

UM108-A/U73 9,65CM S85 - Covering hood



2853828

<https://www.phoenixcontact.com/us/products/2853828>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Press-drawn section housings, Cover, width: 73 mm, Note: max. length of the cover = PCB length - 19 mm

Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2853828 |
| Packing unit | 50 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | ACHDBZ |
| GTIN | 4017918454975 |
| Weight per piece (including packing) | 30.23 g |
| Weight per piece (excluding packing) | 18.53 g |
| Country of origin | DE |

UM108-A/U73 9,65CM S85 - Covering hood



2853828

<https://www.phoenixcontact.com/us/products/2853828>

Technical data

Product properties

| | |
|------------------------------|------------------------------|
| Product type | Component housing cover |
| Housing type | Press-drawn section housings |
| Housing series | UM |
| Product family | UM108 |
| Ventilation openings present | no |

Dimensions

| | |
|-------|-------|
| Width | 73 mm |
|-------|-------|

Material specifications

| | |
|------------------|-------------|
| Color (Housing) | transparent |
| Housing material | PC |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------------|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Relative humidity (storage/transport) | 95 % |

UM108-A/U73 9,65CM S85 - Covering hood



2853828

<https://www.phoenixcontact.com/us/products/2853828>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com