

UM108-A/U73 9,65CM S85 - Covering hood



2853828

<https://www.phoenixcontact.com/us/products/2853828>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Press-drawn section housings, Cover, width: 73 mm, Note: max. length of the cover = PCB length - 19 mm

Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

Item number	2853828
Packing unit	50 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHDBZ
GTIN	4017918454975
Weight per piece (including packing)	30.23 g
Weight per piece (excluding packing)	18.53 g
Country of origin	DE

UM108-A/U73 9,65CM S85 - Covering hood



2853828

<https://www.phoenixcontact.com/us/products/2853828>

Technical data

Product properties

Product type	Component housing cover
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM108
Ventilation openings present	no

Dimensions

Width	73 mm
-------	-------

Material specifications

Color (Housing)	transparent
Housing material	PC
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	95 %

UM108-A/U73 9,65CM S85 - Covering hood



2853828

<https://www.phoenixcontact.com/us/products/2853828>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com