

ME B-22,5 MSTBO GYWH - Filler plug



2853941

<https://www.phoenixcontact.com/us/products/2853941>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug for unoccupied terminal points (MSTBO), width: 20 mm, height: 19.05 mm, depth: 12.3 mm, color: gray white (similar RAL 9002)

Your advantages

- Easy, tool-free mounting
- Flammability rating V0 in accordance with UL 94

Commercial data

Item number	2853941
Packing unit	200 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHAAZ
GTIN	4017918458331
Weight per piece (including packing)	1.288 g
Weight per piece (excluding packing)	1.02 g
Country of origin	DE

ME B-22,5 MSTBO GYWH - Filler plug



2853941

<https://www.phoenixcontact.com/us/products/2853941>

Technical data

Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing series	ME
Ventilation openings present	no

Dimensions

Width	20 mm
Height	19.05 mm
Depth	12.3 mm

Material specifications

Color (Housing)	gray white (RAL 9002)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Latching
---------------	----------

ME B-22,5 MSTBO GYWH - Filler plug

2853941

<https://www.phoenixcontact.com/us/products/2853941>



Classifications

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

ME B-22,5 MSTBO GYWH - Filler plug



2853941

<https://www.phoenixcontact.com/us/products/2853941>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com