

EG 45-AB/PC GN - Upper housing part



2853967

<https://www.phoenixcontact.com/us/products/2853967>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Upper housing part, length: 75 mm, Upper part, color: green, width: 45 mm, height: 17.5 mm



The figure shows a version of the product

Commercial data

Item number	2853967
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	ACHCGA
GTIN	4017918457228
Weight per piece (including packing)	12.9 g
Weight per piece (excluding packing)	11.2 g
Country of origin	PL

EG 45-AB/PC GN - Upper housing part



2853967

<https://www.phoenixcontact.com/us/products/2853967>

Technical data

Product properties

Product type	Upper housing part
Product family	EG...A
Number of positions	16

Dimensions

Width	45 mm
Installed height	17.5 mm
Depth	75 mm
Length	75 mm

Material specifications

Color	green
Flammability rating according to UL 94	V0

EG 45-AB/PC GN - Upper housing part



2853967

<https://www.phoenixcontact.com/us/products/2853967>

Classifications

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

EG 45-AB/PC GN - Upper housing part



2853967

<https://www.phoenixcontact.com/us/products/2853967>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com