

IB IL 24 PWR IN/M - Inline terminal

2861027

<https://www.phoenixcontact.com/us/products/2861027>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Inline power terminal without fuse in acc. with the requirements of Germanic Lloyd (GL)



Your advantages

- Option to tap the protected 24 V voltage, to provide bus terminal supply UBK
- Station protected against conducted surge voltages
- Feed-in or provision of the 24 V segment voltage U_{S}
- Supply of the 24 V main voltage U_{M}
- Diagnostic and status indicators

Commercial data

Item number	2861027
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR01
Product key	DRI121
GTIN	4017918904654
Weight per piece (including packing)	65.7 g
Weight per piece (excluding packing)	51.39 g
Customs tariff number	85389091
Country of origin	DE

IB IL 24 PWR IN/M - Inline terminal



2861027

<https://www.phoenixcontact.com/us/products/2861027>

Technical data

Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps

Product properties

Product type	I/O component
Type	modular
	Inline

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com