

RAD-PIG-EF316-N-N - Antenna cable



2867704

<https://www.phoenixcontact.com/us/products/2867704>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter cable, 50 cm pigtail, N (male) -> N (female), 50 Ω impedance



The figure shows a version of the product

Your advantages

- As an adapter between devices and cables

Commercial data

Item number	2867704
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNN2Z1
GTIN	4017918939076
Weight per piece (including packing)	75.5 g
Weight per piece (excluding packing)	75.5 g
Customs tariff number	85442000
Country of origin	PL

RAD-PIG-EF316-N-N - Antenna cable



2867704

<https://www.phoenixcontact.com/us/products/2867704>

Technical data

Product properties

Product type	Coaxial cable
--------------	---------------

Electrical properties

Frequency range	900 MHz
	2.4 GHz
	5 GHz
Impedance	50 Ω

Connection data

Connector connection

Connection method	N (female)
-------------------	------------

Connector connection

Connection method	N (male)
-------------------	----------

Material specifications

Outer sheath, material	RADOX®(LSFH)
------------------------	--------------

Cable/line

Cable length	50 cm
Cable type	EF 316
External cable diameter	2.50 mm
Outer sheath, material	RADOX®(LSFH)
External sheath, color	blue
Bending radius, long-term	12.50 mm
868 / 900 MHz	0.6 dB
2.4 GHz	1 dB

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com