

# ME MAX 17,5 PLATE KMGY - Insertion plate



2890849

<https://www.phoenixcontact.com/us/products/2890849>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Insertion plate, width: 14.2 mm, height: 73.6 mm, depth: 1 mm, color: light gray (similar RAL 7035)



Product photo shows a standard item

## Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2890849                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 10 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AC22                           |
| Product key                          | ACHABZ                         |
| GTIN                                 | 4046356098281                  |
| Weight per piece (including packing) | 1.41 g                         |
| Weight per piece (excluding packing) | 1.379 g                        |
| Customs tariff number                | 85389099                       |
| Country of origin                    | DE                             |

# ME MAX 17,5 PLATE KMGY - Insertion plate



2890849

<https://www.phoenixcontact.com/us/products/2890849>

## Technical data

### Notes

|               |                                                           |
|---------------|-----------------------------------------------------------|
| Assembly note | Please observe the application note in the download area. |
|---------------|-----------------------------------------------------------|

### Product properties

|                              |                  |
|------------------------------|------------------|
| Product type                 | Cover            |
| Housing type                 | DIN rail housing |
| Housing type                 | Modular housings |
| Housing series               | ME-MAX           |
| Product family               | ME MAX 17,5..    |
| Ventilation openings present | no               |

### Dimensions

|        |         |
|--------|---------|
| Width  | 14.2 mm |
| Height | 73.6 mm |
| Depth  | 1 mm    |

### Material specifications

|                                        |                       |
|----------------------------------------|-----------------------|
| Color (Insertion plate)                | light gray (RAL 7035) |
| Material                               | PA                    |
| Flammability rating according to UL 94 | V0                    |
| CTI according to IEC 60112             | 600                   |

### Mounting

|               |      |
|---------------|------|
| Mounting type | Slot |
|---------------|------|

# ME MAX 17,5 PLATE KMGY - Insertion plate



2890849

<https://www.phoenixcontact.com/us/products/2890849>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2890849>



**UL Recognized**

Approval ID: E240868

# ME MAX 17,5 PLATE KMGY - Insertion plate



2890849

<https://www.phoenixcontact.com/us/products/2890849>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# ME MAX 17,5 PLATE KMGY - Insertion plate



2890849

<https://www.phoenixcontact.com/us/products/2890849>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.013 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)