

# ME MAX 17,5 PLATE KMGY - Insertion plate



2890849

<https://www.phoenixcontact.com/us/products/2890849>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Insertion plate, width: 14.2 mm, height: 73.6 mm, depth: 1 mm, color: light gray (similar RAL 7035)



Product photo shows a standard item

## Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

Item number	2890849
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AC22
Product key	ACHABZ
GTIN	4046356098281
Weight per piece (including packing)	1.41 g
Weight per piece (excluding packing)	1.379 g
Customs tariff number	85389099
Country of origin	DE

# ME MAX 17,5 PLATE KMGY - Insertion plate



2890849

<https://www.phoenixcontact.com/us/products/2890849>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Cover
Housing type	DIN rail housing
Housing type	Modular housings
Housing series	ME-MAX
Product family	ME MAX 17,5..
Ventilation openings present	no

### Dimensions

Width	14.2 mm
Height	73.6 mm
Depth	1 mm

### Material specifications

Color (Insertion plate)	light gray (RAL 7035)
Material	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

### Mounting

Mounting type	Slot
---------------	------

# ME MAX 17,5 PLATE KMGY - Insertion plate



2890849

<https://www.phoenixcontact.com/us/products/2890849>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2890849>



**UL Recognized**

Approval ID: E240868

# ME MAX 17,5 PLATE KMGY - Insertion plate



2890849

<https://www.phoenixcontact.com/us/products/2890849>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME MAX 17,5 PLATE KMGY - Insertion plate



2890849

<https://www.phoenixcontact.com/us/products/2890849>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)