

IBS IL 24 RB-T-PAC/10 - Branch terminal



2897444

<https://www.phoenixcontact.com/us/products/2897444>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Branch terminal, transmission speed in the local bus: 500 kbps, degree of protection: IP20

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2897444 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | DR19 |
| Product key | DRI152 |
| GTIN | 4046356138949 |
| Weight per piece (including packing) | 80 g |
| Weight per piece (excluding packing) | 67 g |
| Customs tariff number | 85389091 |
| Country of origin | DE |

2897444

<https://www.phoenixcontact.com/us/products/2897444>

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Interfaces

Inline local bus

| | |
|----------------------|--------------------|
| Connection method | Inline data jumper |
| Transmission speed | 500 kbps |
| Transmission physics | Copper |

Product properties

| | |
|----------------|---------------|
| Product type | I/O component |
| Product family | Inline |
| Type | modular |

Connection data

| | |
|-------------------|------------------------|
| Connection method | Spring-cage connection |
| Stripping length | 8 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP20 |
|----------------------|------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

2897444

<https://www.phoenixcontact.com/us/products/2897444>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242608 |
| ECLASS-15.0 | 27242608 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001604 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32151600 |
|-------------|----------|

2897444

<https://www.phoenixcontact.com/us/products/2897444>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com