

PLC-BSC-230UC/21-CRY - Basic terminal block



2900801

<https://www.phoenixcontact.com/us/products/2900801>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2900801 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | DK621X |
| GTIN | 4046356543699 |
| Weight per piece (including packing) | 28.19 g |
| Weight per piece (excluding packing) | 28.19 g |
| Customs tariff number | 85364900 |
| Country of origin | DE |

PLC-BSC-230UC/21-CRY - Basic terminal block



2900801

<https://www.phoenixcontact.com/us/products/2900801>

Technical data

Product properties

| | |
|----------------|---------------|
| Product type | Relay socket |
| Product family | PLC-INTERFACE |

Connection data

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 2.5 mm ² |
| | 0.2 mm ² ... 2.5 mm ² (Single ferrule) |
| | 2x 0.5 mm ² ... 1.5 mm ² (TWIN ferrule) |
| Conductor cross-section AWG | 26 ... 14 |
| Tightening torque | 0.6 Nm ... 0.8 Nm |

Mounting

| | |
|-------------------|-------------------|
| Mounting type | DIN rail mounting |
| Mounting position | any |

PLC-BSC-230UC/21-CRY - Basic terminal block



2900801

<https://www.phoenixcontact.com/us/products/2900801>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122335 |
|-------------|----------|

2900801

<https://www.phoenixcontact.com/us/products/2900801>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | Hexahydromethylphthalic anhydride(CAS: n/a) |
| | Lead(CAS: 7439-92-1) |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com