
VF-SI/TR5/0,063AT - Fuse set

2901004

https://www.phoenixcontact.com/us/products/2901004

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse set, number: 8 Pcs., fuse type: Fuse (TR5), nominal current: 0.063 A, tripping characteristic: slow-blow (T)

Commercial data

Item number	2901004
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK218Z
GTIN	4046356557177
Weight per piece (including packing)	5.8 g
Weight per piece (excluding packing)	0.57 g
Customs tariff number	85361010
Country of origin	DE

Technical data

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

Product properties

Product type	Fuse
Number of fuses in the set	8

Electrical properties

Tripping characteristic	slow-blow (T)
Maximum power dissipation for nominal condition	0.2 W
Nominal voltage U_N	250 V
Nominal current I_N	0.063 A
Fuse rating	TR5
Fuse	Fuse

Dimensions

Dimensions	8.5 x 8 mm

Classifications

ECLASS

ECLASS-13.0	27142002
ECLASS-15.0	27142002

ETIM

ETIM 9.0	EC002704

UNSPSC

UNSPSC 21.0	39121600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com