

# ME MAX 45 PLATE KMGY - Insertion plate



2901123

<https://www.phoenixcontact.com/us/products/2901123>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Insertion plate, width: 41.8 mm, height: 73.6 mm, depth: 1 mm, color: light gray (similar RAL 7035)



## Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2901123                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 10 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AC08                           |
| Product key                          | ACHABZ                         |
| GTIN                                 | 4046356353601                  |
| Weight per piece (including packing) | 3.66 g                         |
| Weight per piece (excluding packing) | 3.61 g                         |
| Customs tariff number                | 85389099                       |
| Country of origin                    | DE                             |

# ME MAX 45 PLATE KMGY - Insertion plate



2901123

<https://www.phoenixcontact.com/us/products/2901123>

## Technical data

### Product properties

|                              |                  |
|------------------------------|------------------|
| Product type                 | Cover            |
| Housing type                 | DIN rail housing |
| Housing type                 | Modular housings |
| Housing series               | ME-MAX           |
| Product family               | ME MAX 45..      |
| Ventilation openings present | no               |

### Dimensions

|        |         |
|--------|---------|
| Width  | 41.8 mm |
| Height | 73.6 mm |
| Depth  | 1 mm    |

### Material specifications

|  |                       |
|--|-----------------------|
| Color (Insertion plate)                | light gray (RAL 7035) |
| Material                               | PA                    |
| Flammability rating according to UL 94 | V0                    |
| CTI according to IEC 60112             | 600                   |

### PCB data

|                   |          |
|-------------------|----------|
| Type of PCB mount | Latching |
|-------------------|----------|

### Mounting

|               |      |
|---------------|------|
| Mounting type | Slot |
|---------------|------|

# ME MAX 45 PLATE KMGY - Insertion plate



2901123

<https://www.phoenixcontact.com/us/products/2901123>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2901123>



**UL Recognized**

Approval ID: E240868

# ME MAX 45 PLATE KMGY - Insertion plate



2901123

<https://www.phoenixcontact.com/us/products/2901123>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# ME MAX 45 PLATE KMGY - Insertion plate



2901123

<https://www.phoenixcontact.com/us/products/2901123>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.028 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)