

EEM-PB-MA600 - Communication module



2901368

<https://www.phoenixcontact.com/us/products/2901368>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

PROFIBUS (1.5 Mbps) communication module for EEM-MA600



Your advantages

- PROFIBUS DP, with transmission speeds of 1.5 or 12 Mbps

Commercial data

Item number	2901368
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C440
Product key	CMMC11
GTIN	4046356584234
Weight per piece (including packing)	171.2 g
Weight per piece (excluding packing)	171.2 g
Customs tariff number	90303100
Country of origin	FR

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Communication module
Insulation characteristics	
Overvoltage category	III (For mains voltage <300 V AC (L/N)) II (for mains voltage >300 V AC ... 600 V AC (L/N))
Pollution degree	2

Electrical properties

Electrical isolation	EN 61010-1 (Safe isolation) EN 61010-1 (Safe isolation)
Test voltage	3.5 kV AC (50 Hz, 1 min.)

Supply

Supply voltage	9 V (via EEM-MA600)
----------------	---------------------

Connection data

Connection method	COMBICON plug-in screw terminal block
Stripping length	6 mm
Conductor cross-section rigid	0.5 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross-section AWG	20 ... 14
Tightening torque	0.4 Nm ... 0.4 Nm

Interfaces

Data: PROFIBUS DP

Interface	RS-485
Serial transmission speed	9.6 kbps ... 1.5 Mbps
Connection method	COMBICON plug-in screw terminal block
Connection technology	2-, 3-conductor
Transmission length	≤ 100 m

Data

Communication protocol	PROFIBUS DP
Communication standard	RS-485
Connection method	COMBICON plug-in screw terminal block
Transmission speed range	9.6 kbps ... 1.5 Mbps (Serial)

2901368

<https://www.phoenixcontact.com/us/products/2901368>

Dimensions

Width	22.5 mm
Height	65 mm
Depth	48 mm

Material specifications

Color	black (RAL 9005)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 55 °C (14 °F ... 131 °F)
Ambient temperature (storage/transport)	-20 °C ... 85 °C (-4 °F ... 185 °F)
Max. permissible relative humidity (operation)	≤ 95 %
Max. salt spray content	≤ 2.5 %

Approvals

CE

Certificate	CE-compliant
-------------	--------------

UL, USA/Canada

Identification	UL 61010-1
	CSA-C22.2 No. 61010-1
	cULus

EEM-PB-MA600 - Communication module



2901368

<https://www.phoenixcontact.com/us/products/2901368>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com